

Rittal – The System.

Faster – better – everywhere.



SG 2372.011

LED komponenta za stalno svetlobo

State: 11.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.011 - LED komponenta za stalno svetlobo za signalni steber, modularno

S 360° oddajanjem signala zahvaljujoč optimizirani tehnologiji prizme.

Features

Št. Modela	SG 2372.011
Zasnova	LED komponenta za stalno svetlobo
Prednosti	S 360° prenosom signala z optimiziranim sistemom prizem Konfiguracija do petih komponent z enako napetostjo.
Način delovanja	Možna je modularna zasnova s priključki, optičnimi in akustičnimi komponentami ter označevalno ploščo
Material	Ohišje iz poliamida Pokrovček: prozoren polikarbonat
Barva	Zelena
Razred zaščite po IEC 60 529	IP 65 if a cover or acoustic component is fitted at the top
Nazivna delovna napetost	24 V (AC/DC)
Paketi	1 pc(s).
Neto teža	0,072 kg
Bruto teža	0,073 kg
Carinska tarifna številka	85311095
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220
Opis izdelka	SG LED steady light component, green

Approvals

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
