

Rittal – The System.

Faster – better – everywhere.



SG 2372.130

Kompaktni LED signalni steber

State: 6.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.130 - Kompaktni LED signalni steber

Extremely long service life of the LEDs, minimal assembly work and low warehousing costs.

Features

Št. Modela	SG 2372.130
Zasnova	1-stopenjska, rdeča
Prednosti	Popolna rešitev, pripravljena za priklop Minimalna višina konstrukcije Dolga življenjska doba LED luči Minimalni stroški montaže in skladiščenja
Kabelske uvodnice	Min. premer kabla: 3 mm Maks. premer kabla: 6,5 mm
Premer	72 mm
Vrsta električne povezave	Screw terminals
Luči	LEDs
Nazivna izolacijska napetost	< 60 V DC
Mere	Višina: 107 mm
Delovno temperaturno območje	-20 °C...70 °C
Razred zaščite po IEC 60 529	IP 65
Nazivna delovna napetost	24 V 24 V (DC)
Paketi	1 pc(s).
Neto teža	0,219 kg
Bruto teža	0,233 kg
Carinska tarifna številka	85311095
ECLASS 8.0	27371230
Opis izdelka	SG Signal pillar, LED-compact, 24 V AC/DC, 1-stage, red

Approvals

Approvals

UR

Explanations

Declaration of conformity

Declaration of conformity UK