

# Rittal – The System.

Faster – better – everywhere.



## AE 2383.300 Rail for interior installation

State: 4.4.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 2383.300 - Rail for interior installation for AE/WM

For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



## Features

|                       |  |
|-----------------------|--|
| Model No.             | AE 2383.300  |
| Product description   | For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable with 2 rows of system punchings, creates additional mounting space e.g. for: TS punched section, enclosure lights, door-operated switch, door stay, cable conduit holder |
| Material              | Sheet steel  |
| Surface finish        | Zinc-plated  |
| Note                  | Other mounting options: Mounting plates, locatable, TS 8612.400<br>Mounting plates, screw-fastening, large, TS 8612.410<br>Mounting plates, screw-fastening, small, PS 4532.000<br>Mounting bracket, PS 4597.000   |
| To fit                | Enclosure type: AE<br>Depth: = 300 mm  |
| Packs of              | 4 pc(s).   |
| Net weight            | 0,8 kg   |
| Gross weight          | 0,92 kg  |
| Customs tariff number | 73269098   |
| ETIM 9                | EC002625   |
| ETIM 8                | EC002625   |

# Features

---

ECLASS 8.0

27189234

---

Product description

AE Rail for interior installation, for AE, for D: 300 mm