

# Rittal – The System.

Faster – better – everywhere.



## SZ 2411.601

# Kabelska uvodnica, poliamid

State: 9.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.601 - Kabelska uvodnica, poliamid

Integrirane vpenjalne membrane zagotavljajo zanesljivo privijanje in razbremenitev napetosti za zaščito kablov.

## Features

Št. Modela	SZ 2411.601
Prednosti	Ker se uvodnice in varovalna matica prodajajo skupaj v enem paketu, to prihrani dodatno naročanje in shranjevanje. Vpenjalne membrane za enakomerno zategovanje in razbremenitev napetosti za zaščito kablov
Material	Poliamid 6 Tesnilo: CR/NBR
Barva	RAL 7035
IP razred zaščite po IEC 60 529	IP 68 (5 bar, 30 min)
Mere	Višina: 22 mm
Navoj	M12 x 1.5
Dolžina navoja	8 mm
Min. premer kabla	3 mm
Maks. premer kabla	6,5 mm
Delovno temperaturno območje	-30 °C...100 °C
torque	1,8 Nm
Širina med ploščami	15 mm
Mere	Navoj: M12 x 1.5 Dolžina navoja: 8 mm
Tipska ocena po UL 50E	Type 4X
Paketi	50 pc(s).
Neto teža	0,05 kg
Bruto teža	0,22 kg

# Features

---

Carinska tarifna številka	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Opis izdelka	SZ Cable gland, polyamide, size: M12x1,5, for cables ø 3-6.5 mm

---

# Approvals

---

Approvals	CSA + CSAus UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK

---