

Rittal – The System.

Faster – better – everywhere.



SZ 2411.611

Kabelska uvodnica, poliamid

State: 9.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.611 - Kabelska uvodnica, poliamid

Integrirane vpenjalne membrane zagotavljajo zanesljivo privijanje in razbremenitev napetosti za zaščito kablov.

Features

Št. Modela	SZ 2411.611
Prednosti	Ker se uvodnice in varovalna matica prodajajo skupaj v enem paketu, to prihrani dodatno naročanje in shranjevanje. Vpenjalne membrane za enakomerno zategovanje in razbremenitev napetosti za zaščito kablov
Material	Poliamid 6 Tesnilo: CR/NBR
Barva	RAL 7035
IP razred zaščite po IEC 60 529	IP 68 (5 bar, 30 min)
Mere	Višina: 30 mm
Navoj	M16 x 1.5
Dolžina navoja	10 mm
Min. premer kabla	5 mm
Maks. premer kabla	10 mm
Delovno temperaturno območje	-30 °C...100 °C
torque	2,5 Nm
Širina med ploščami	22 mm
Mere	Navoj: M16 x 1.5 Dolžina navoja: 10 mm
Tipska ocena po UL 50E	Type 4X
Paketi	50 pc(s).
Neto teža	0,5 kg
Bruto teža	0,546 kg

Features

Carinska tarifna številka	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Opis izdelka	SZ Cable gland, polyamide, size: M16x1,5, for cables ø 5-10 mm

Approvals

Approvals	CSA + CSAus UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK
