

# Rittal – The System.

Faster – better – everywhere.



## SZ 2411.631

# Kabelska uvodnica, poliamid

State: 8.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.631 - Kabelska uvodnica, poliamid

Integrirane vpenjalne membrane zagotavljajo zanesljivo privijanje in razbremenitev napetosti za zaščito kablov.

## Features

Št. Modela	SZ 2411.631
Prednosti	Ker se uvodnice in varovalna matica prodajajo skupaj v enem paketu, to prihrani dodatno naročanje in shranjevanje. Vpenjalne membrane za enakomerno zategovanje in razbremenitev napetosti za zaščito kablov
Material	Poliamid 6 Tesnilo: CR/NBR
Barva	RAL 7035
IP razred zaščite po IEC 60 529	IP 68 (5 bar, 30 min)
Mere	Višina: 35,5 mm
Navoj	M25 x 1.5
Dolžina navoja	8 mm
Min. premer kabla	10 mm
Maks. premer kabla	17 mm
Delovno temperaturno območje	-30 °C...100 °C
torque	5 Nm
Širina med ploščami	29 mm
Mere	Navoj: M25 x 1.5 Dolžina navoja: 8 mm
Tipska ocena po UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Paketi	25 pc(s).

## Features

---

Neto teža	0,475 kg
Bruto teža	0,495 kg
Carinska tarifna številka	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Opis izdelka	SZ Cable gland, polyamide, size: M25x1,5, for cables ø 10-17 mm

## Approvals

---

Approvals	CSA + CSAus UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK