

Rittal – The System.

Faster – better – everywhere.



SZ 2411.651

Kabelska uvodnica, poliamid

State: 11.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.651 - Kabelska uvodnica, poliamid

Integrirane vpenjalne membrane zagotavljajo zanesljivo privijanje in razbremenitev napetosti za zaščito kablov.

Features

Št. Modela	SZ 2411.651
Prednosti	Ker se uvodnice in varovalna matica prodajajo skupaj v enem paketu, to prihrani dodatno naročanje in shranjevanje. Vpenjalne membrane za enakomerno zategovanje in razbremenitev napetosti za zaščito kablov
Material	Poliamid 6 Tesnilo: CR/NBR
Barva	RAL 7035
IP razred zaščite po IEC 60 529	IP 68 (5 bar, 30 min)
Mere	Višina: 47,5 mm
Navoj	M40 x 1.5
Dolžina navoja	10 mm
Min. premer kabla	19 mm
Maks. premer kabla	28 mm
Delovno temperaturno območje	-30 °C...100 °C
torque	12 Nm
Širina med ploščami	46 mm
Mere	Navoj: M40 x 1.5 Dolžina navoja: 10 mm
Tipska ocena po UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Paketi	5 pc(s).

Features

Neto teža	0,25 kg
Bruto teža	0,28 kg
Carinska tarifna številka	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Opis izdelka	SZ Cable gland, polyamide, size: M40x1,5, for cables ø 19-28 mm

Approvals

Approvals	CSA + CSAus UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK
