

Rittal – The System.

Faster – better – everywhere.



SZ 2411.651

Kabelska uvodnica, poliamid

State: 8.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.651 - Kabelska uvodnica, poliamid

Integrirane vpenjalne membrane zagotavljajo zanesljivo privijanje in razbremenitev napetosti za zaščito kablov.

Features

| | |
|---------------------------------|---|
| Št. Modela | SZ 2411.651 |
| Prednosti | Ker se uvodnice in varovalna matica prodajajo skupaj v enem paketu, to prihrani dodatno naročanje in shranjevanje. Vpenjalne membrane za enakomerno zategovanje in razbremenitev napetosti za zaščito kablov |
| Material | Poliamid 6 Tesnilo: CR/NBR |
| Barva | RAL 7035 |
| IP razred zaščite po IEC 60 529 | IP 68 (5 bar, 30 min) |
| Mere | Višina: 47,5 mm |
| Navoj | M40 x 1.5 |
| Dolžina navoja | 10 mm |
| Min. premer kabla | 19 mm |
| Maks. premer kabla | 28 mm |
| Delovno temperaturno območje | -30 °C...100 °C |
| torque | 12 Nm |
| Širina med ploščami | 46 mm |
| Mere | Navoj: M40 x 1.5 Dolžina navoja: 10 mm |
| Tipska ocena po UL 50E | Type 1 Type 4 Type 4X Type 12 Type 13 |
| Paketi | 5 pc(s). |

Features

| | |
|---------------------------|---|
| Neto teža | 0,25 kg |
| Bruto teža | 0,28 kg |
| Carinska tarifna številka | 39269097 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Opis izdelka | SZ Cable gland, polyamide, size: M40x1,5, for cables ø 19-28 mm |

Approvals

| | |
|--------------|---|
| Approvals | CSA + CSAus UL + C-UL (listed) VDE |
| Explanations | Declaration of conformity Declaration of conformity UK |
