

Rittal – The System.

Faster – better – everywhere.



SZ 2488.000 Samorezni vijaki

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2488.000 - Samorezni vijaki

Za okrogle luknje s premerom 4,5 mm v ohišju, luknjane tirnice in luknjane profile brez montažnih prirobnic.

Features

Št. Modela	SZ 2488.000
Zasnova	Križni vijaki z ugreznjeno glavo
Aplikacije	Za okrogle luknje Ø 4,5 ali 4,7 mm v delu ohišja, luknjane tirnice in luknjane profile brez montažnih prirobnic
Mere	Navoj: M5 Dolžina navoja: 12 mm
Navoj	M5
Paketi	500 pc(s).
Neto teža	0,5 kg
Bruto teža	0,844 kg
Carinska tarifna številka	73181900
ETIM 9	EC000891
ETIM 8	EC000891
ECLASS 8.0	23110117
Opis izdelka	SZ Posidrive raised countersunk screws, for thread M5, self-tapping