

Rittal – The System.

Faster – better – everywhere.



SZ 2500.470 Stikalo za vrata

State: 26.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.470 - Stikalo za vrata za LED sistemsko luč

Za enostavno in hitro namestitev LED sistemske luči.

Features

Št. Modela	SZ 2500.470
Zasnova	S priključnim kablom
Opis izdelka	Za prihranek časa in enostaven priklop LED sistemske luči.
Barva	Črna
Obseg dobave	Sestavni deli
Prečni prerez	0,75 mm ²
Dolžina	800 mm
AWG	AWG 18
Standardi	Napajalni kabli: CYJV2 Stikalo za vrata: NKCR
Mere	Širina: 31 mm Višina: 78 mm Globina: 30 mm Dolžina: 800 mm
Električna povezava	2,5 A
Nazivna delovna napetost	230 V (AC) 24 V (DC)
Paketi	1 pc(s).
Neto teža	0,1 kg
Bruto teža	0,11 kg
Carinska tarifna številka	85365019
ETIM 9	EC002626
ETIM 8	EC002626
ECLASS 8.0	27189266

Features

Opis izdelka

SZ Door-operated switch, with connection wire, L: 800 mm, black, UL

Approvals

Approvals

CQC
CQC-CCC
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK