

Rittal – The System.

Faster – better – everywhere.



SZ 2560.010

Plastic cable gland plates

State: 8.12.2025 (Source: [rittal.com/si-si](https://www.rittal.com/si-si))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2560.010 - Plastic cable gland plates with metric knockouts

With pre-punched holes for cable glands.

Features

Model No.	SZ 2560.010
Product description	With pre-punched holes for cable glands. Use seal for standard gland plates.
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	2 x M12 2 x M20 3 x M25
Dimensions	Width: 160 mm Depth: 70 mm
To fit	Enclosure type: AE
Gland plate	Size: 1
Operating temperature range	-40 °C...70 °C
Protection category to IEC 60 529	IP 55 if installed correctly
Number knockouts	2 2 3
Metric diameter	M12 M20 M25
Packs of	10 pc(s).
Net weight	0.51
Gross weight	0.605

Features

Customs tariff number	39269097
EAN	4028177550254
E-Number Sweden	E3404761
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421