

Rittal – The System.

Faster – better – everywhere.



SZ 2562.500

Plastic cable gland plates

State: 6.9.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2562.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

Features

| | |
|----------------------------------------------|-----------------------------------------------------------------------------|
| Model No. | SZ 2562.500 |
| Product description | Simply pierce the plastic with a sharp object, and pull through the cable. |
| Material | Plastic to UL 94-V0 Halogen free |
| Colour | Similar to RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| Dimensions | Width: 339 mm Depth: 149 mm |
| To fit | Enclosure type: AE |
| Gland plate | Size: 4 |
| Protection category to IEC 60 529 | IP 65 |
| No. of cable entries and Ø (mm) min.-max. | 24 x 7-12 48 x 10-15 4 x 15-21 8 x 15-25 4 x 26-35 |
| Packs of | 1 pc(s). |
| Net weight | 0.55 |
| Gross weight | 0.58 |
| Customs tariff number | 39269097 |
| EAN | 4028177325609 |
| E-Number Sweden | E3404728 |

Features

| | |
|------------|----------|
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |