


Rittal – The System.

Faster – better – everywhere.



SK 3124.010 Omrežna dušilka

State: 21.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3124.010 - Omrežna dušilka Stenska hladilna enota Blue e+ Dynamic

Omrežna dušilka za skladnost z EMC zahtevami po DNV-CG-0339 razreda A.

Features

Št. Modela	SK 3124.010
Paketi	1 pc(s).
Za model št.	3184.837 / 3484.837 3185.837 / 3485.837 3186.937 / 3486.937 3187.937 / 3487.937
Mere	Širina: 40 mm Višina: 44 mm Dolžina: 76 mm
Delovno temperaturno območje	0 °C...85 °C
Nazivna delovna napetost	230 V, 1~, 50 Hz/60 Hz
IP razred zaščite po IEC 60 529	IP 00
Neto teža	0,3 kg
Bruto teža	0,382 kg
Carinska tarifna številka	85059090
Opis izdelka	SK line reactor, for Blue e+ Dynamic wall-mounted cooling unit, 230 V, 1~, 50/60 Hz