

Rittal – The System.

Faster – better – everywhere.



SK 3124.010 Line reactor

State: 24.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3124.010 - Line reactor Wall-mounted cooling unit Blue e+ Dynamic

Line reactor for complying with EMC requirements to DNV-CG-0339 Class A.

Features

Model No.	SK 3124.010
Packs of	1 pc(s).
To fit Model No.	3184.837 3185.837 3186.937 3187.937
Dimensions	Width: 40 mm Height: 44 mm Length: 76 mm
Operating temperature range	0 °C...85 °C
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
IP protection category to IEC 60529	IP 00
Net weight	0.3
Gross weight	0.382
Customs tariff number	85059090
EAN	4028177039483