

# Rittal – The System.

Faster – better – everywhere.



## SK 3164.230 Strešni ventilatorji

State: 19.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3164.230 - Strešni ventilatorji za VX, VX IT

Roof-mounted fan for the office sector with exceptionally low noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m<sup>3</sup>/h).



## Features

Št. Modela	SK 3164.230
Prednosti	Enostavna montaža, različica strešne plošče odpravlja potrebo po izrezovanju montažnih odprtin Popolnoma ožičeno, pripravljeno za priklop
Material	Jeklena pločevina, lakirano
Barva	RAL 7035
Obseg dobave	Strešni ventilatorji Sestavni deli
Nazivna delovna napetost	230 V, 1~, 50 Hz/60 Hz
Maks. nazivni tok	Pri 50 Hz: 0,3 A Pri 60 Hz: 0,35 A
Mere	Širina: 511 mm Višina: 227 mm Globina: 511 mm
IP razred zaščite po IEC 60 529	Internal circuit IP 54
Opomba	Zmanjšanje predpisanega pretoka zraka na 800 m <sup>3</sup> /h pri protitlaku 40 Pa z uporabo dveh prezračevanih zaključnih plošč podnožja/ podstavka
Delovno temperaturno območje	20 °C...55 °C
Paketi	1 pc(s).

# Features

---

Neto teža	18,35 kg
Bruto teža	19,36 kg
Carinska tarifna številka	84145915
ECLASS 8.0	27180716
Opis izdelka	DK Roof-mounted fan, without roof plate, for TS and TS IT in the office sector, Required mounting cut-out: WxD: 410x410 mm, WHD: 511x227x511 mm

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---