

Rittal – The System.

Faster – better – everywhere.



SK 3201.900 Priključek G $\frac{3}{8}$ "

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3201.900 - Priključek G 3/8"

Notranji navojni adapter G 3/8" se lahko uporabi za izdelavo fiksnih cevi na toplotnem izmenjevalniku zrak/voda za dovod in povratni vod.

Features

Št. Modela	SK 3201.900
Opis izdelka	Z adapterjem z notranjim navojem G 3/8" lahko ustvarite fiksno cevno povezavo za dovod in povratni vod na toplotnem izmenjevalniku zrak/voda.
Material	Medenina
Zasnova ventila	G3/8" internal thread
Za model št.	3209.... 3210.... 3363.... 3364.... 3373.... 3374.... 3375....
OUT_PRESSURE_ADJUSTMENT_RANGE	1 - 10 bar
Paketi	2 pc(s).
Neto teža	0,13 kg
Bruto teža	0,131 kg
Carinska tarifna številka	83015000
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Opis izdelka	SK Fitting, for Air/water heat exchanger , G 3/8" internal thread adaptor, Pressure setting range: 1-10 bar