

Rittal – The System.

Faster – better – everywhere.



SK 3238.200 Izhodni filter

State: 28.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3238.200 - Izhodni filter Standardne

Za prezračevanje s konvekcijo je mogoče v zgornji in spodnji del ohišja namestiti izhodni filter.



Features

Št. Modela	SK 3238.200
Opis izdelka	Za prezračevanje s konvekcijo se lahko v spodnjem in zgornjem delu ohišja uporabi izhodni filter.
Material	ABS
Barva	RAL 7035
Obseg dobave	Izhodni filter Filtrirna podloga iz sesekljanih vlaken
Izrez za montažo	Širina izreza: 124 mm Višina izreza: 124 mm
Za model št.	SK 3238.1xx
Mere	Širina: 148,5 mm Višina: 148,5 mm Globina: 24 mm
Razred zaščite NEMA	Type 1 with pleated filter Type 12 with chopped-fibre filter Type 3 Type 3R Type 4 Type 4X with chopped-fibre filter/pleated filter and hose-proof hood
IP razred zaščite po IEC 60 529	IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood

Features

Paketi	1 pc(s).
Neto teža	0,17 kg
Bruto teža	0,18 kg
Carinska tarifna številka	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Opis izdelka	SK outlet filter, Standard, WHD: 148.5 x 148.5 x 24 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity