

# Rittal – The System.

Faster – better – everywhere.



## SK 3240.208 Izhodni filter

State: 2.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3240.208 - Izhodni filter Standardne

Za prezračevanje s konvekcijo je mogoče v zgornji in spodnji del ohišja namestiti izhodni filter.



## Features

|                                 |  |
|---------------------------------|--|
| Št. Modela                      | SK 3240.208  |
| Opis izdelka                    | Za prezračevanje s konvekcijo se lahko v spodnjem in zgornjem delu ohišja uporabi izhodni filter.  |
| Material                        | ABS  |
| Barva                           | RAL 9005   |
| Obseg dobave                    | Izhodni filter<br>Filtrirna podloga iz sesekljanih vlaken  |
| Izrez za montažo                | Širina izreza: 224 mm<br>Višina izreza: 224 mm   |
| Za model št.                    | 3240.1xx/3240.5xx/3241.1xx/3241.5xx  |
| Mere                            | Širina: 255 mm<br>Višina: 255 mm<br>Globina: 25 mm   |
| Razred zaščite NEMA             | Type 12 with chopped-fibre filter/pleated filter<br>Type 3<br>Type 3R<br>Type 4<br>Type 4X with chopped-fibre filter/pleated filter and hose-proof hood            |
| IP razred zaščite po IEC 60 529 | IP 54 with chopped-fibre filter/pleated filter<br>IP 55 with pleated filter and absorber mat<br>IP 56 with chopped-fibre filter/pleated filter and hose-proof hood |

# Features

---

|                           |  |
|---------------------------|--|
| Paketi                    | 1 pc(s).   |
| Neto teža                 | 0,46 kg  |
| Bruto teža                | 0,56 kg  |
| Carinska tarifna številka | 39269097   |
| ETIM 9                    | EC002513   |
| ETIM 8                    | EC002513   |
| ECLASS 8.0                | 27180716   |
| Opis izdelka              | SK outlet filter, standard, WHD: 255 x 255 x 25 mm |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL - FTTA<br>UR + C-UR (recognized)                |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |