
Rittal - The System.

Faster – better – everywhere.





SK 3243.308 Blue e+ outlet filter

State: 21.11.2025 (Source: rittal.com/si-sl)




SK 3243.308 - Blue e+ outlet filter

The outlet filter is used in conjunction with the corresponding fan-and-filter unit to dissipate heat loss from enclosures, ventilate the enclosure and protect temperature-sensitive components. This is achieved through the direct infeed of ambient air, the temperature of which must be lower than the permissible internal temperature of the enclosure.







Features

Model No.	SK 3243.308
Design	wall-mounted
Benefits	Easy filter changes, thanks to a new opening mechanism on the
	louvred grille
	Faster installation on the enclosure with optimised detent hooks
	Tool-free assembly
Material	Plastic
Colour	RAL 9005
Supply includes	Outlet filter
	Pleated filter
Mounting cut-out	Cut-out width: 292 mm
	Cut-out height: 292 mm
To fit Model No.	SK 3243.7xx/3243.9xx/3244.7xx/3244.9xx/3245.9xx
Dimensions	Width: 323 mm
	Height: 323 mm
	Depth: 44.7 mm

© Rittal 2025 2

Features

Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose- proof hood
IP protection category to IEC 60	IP 54 with chopped-fibre filter/pleated filter
529	IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Packs of	1 pc(s).
Net weight	0.94
Gross weight	0.95
Customs tariff number	39269097
EAN	4028177998322
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UL + C-UL - FTTA
	UR + C-UR (recognized)

© Rittal 2025 3