


Rittal – The System.

Faster – better – everywhere.



SK 3301.320

Vertical shielding

State: 30.7.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3301.320 - Vertical shielding for TS IT

To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.

Features

| | |
|-----------------------|---|
| Model No. | SK 3301.320 |
| Design | Self-adhesive on one side |
| Product description | To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm. |
| Material | Cellular PU foam Flame-inhibiting to UL 94 (HF1) |
| Colour | Anthracite |
| Sealing between | LCP and 482.6 mm (19") level |
| Dimensions | Width: 210 mm Height: 1,915 mm Depth: 110 mm |
| To fit | Width: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.135 |
| Gross weight | 1.335 |
| Customs tariff number | 39269097 |
| EAN | 4028177504424 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |

Tender text

Thick foam rubber, 800 mm rack, vertical LCP shielding

Cellular PU foam, flame-inhibiting to UL 94 (HF1) to block the airflow on the left and right of the 482.6 mm (19 inch) level. For 800 mm wide enclosures. Length: 1900 mm, self-adhesive