

# Rittal – The System.

Faster – better – everywhere.



## SK 3301.390

## Navpična pregrada

State: 2.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3301.390 - Navpična pregrada za TS IT

Za blokiranje pretoka zraka na levi in desni strani 482,6 mm (19") nivoja, za ohišja z višino 2000 mm.

## Features

Št. Modela	SK 3301.390
Zasnova	Samolepilno na eni strani
Opis izdelka	Za zaporo pretoka zraka levo in desno od 19" ravnine pri ohišjih z višino 2000 mm.
Material	Celična PU pena Odporno proti ognju po UL 94 (HF1)
Barva	Antracit
Tesnjenje med	Side panel and 482.6 mm (19") level
Mere	Širina: 184 mm Višina: 1.910 mm Globina: 84 mm
Primerno za	Širina: 800 mm
Paketi	1 pc(s).
Neto teža	0,818 kg
Bruto teža	0,918 kg
Carinska tarifna številka	39269097
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Opis izdelka	SK Vertical shielding, Sealing between side panel/LCP and 482.6 mm (19") level, WHD: 184x1910x84 mm, Cellular PU foam, self-adhesive on one side