

Rittal – The System.

Faster – better – everywhere.



SK 3301.612

Cev za kondenzat

State: 27.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3301.612 - Cev za kondenzat

Za odvajanje kondenzata. Za priklop na hladilne enote ohišij in toplotne izmenjevalnike zrak/voda.

Features

Št. Modela	SK 3301.612
Opis izdelka	Za odvajanje in transport kondenzata. Za priklop na hladilne enote krmilnega ohišja in toplotne izmenjevalnike zrak/voda.
Material	PVC, prozorno
Premer	12 mm
Dolžina	10 m
Debelina materiala	2 mm

Features

Za model št.	3209...3210 3214.100 3215.100 3216.480 3273.... 3304...3305 3328...3329 3332.... 3359.... 3363...3364 3366.... 3373...3375 3377...3378 3382...3385 3386...3387 3178.80x / 3478.80x 3179.80x / 3479.80x 3180.800 / 3480.800 3184.8x0 / 3484.8x0 3185.xxx / 3485.xxx 3186.xxx / 3486.xxx 3187.xxx / 3487.xxx 3188.xxx / 3488.xxx 3189.xxx / 3489.xxx
--------------	---

Mere	Dolžina: 10 m
------	---------------

Paketi	1 pc(s).
--------	----------

Neto teža	1 kg
-----------	------

Bruto teža	1,03 kg
------------	---------

Carinska tarifna številka	40094200
---------------------------	----------

ETIM 9	EC002009
--------	----------

ETIM 8	EC002009
--------	----------

ECLASS 8.0	27180715
------------	----------

Opis izdelka	SK Condensate hose, Ø 12 x 2 mm, length 10 m
--------------	--