

Rittal – The System.

Faster – better – everywhere.



SK 3312.815

Vrata iz jeklene pločevine

State: 28.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3312.815 - Vrata iz jeklene pločevine za stensko hladilno enoto Blue e+ IT

Za namestitev stenske hladilne enote. Izrez v vratih je razporejen tako, da je stenska hladilna enota nameščena na sredini vrat.

Features

Št. Modela	SK 3312.815
Material	Jeklena pločevina
Površinska obdelava	lakirano
Barva	RAL 7035
Obseg dobave	Zadnja vrata iz jeklene pločevine Udoben ročaj za profilne polcilindre z varnostno ključavnico 3524 E Montažni deli (z zaklepnimi deli, vendar brez tečajev)
Za model št.	3312.810 / 3412.810 3186.x3x / 3486.x3x 3187.x3x / 3487.x3x 3188.x4x / 3488.x4x 3189.x4x / 3489.x4x
Mere	Širina: 600 mm Višina: 2.000 mm
Primerno za	Vrsta ohišja: VX IT VX
Paketi	1 pc(s).
Neto teža	13 kg
Bruto teža	15 kg
Carinska tarifna številka	94039910
ETIM 9	EC002510
ETIM 8	EC000744
ECLASS 8.0	27182405

Features

Opis izdelka

SK IT sheet steel door, for VX IT, with mounting cut-out for cooling unit 3312.810/3412.810, WxD: 600x2000 mm, RAL 7035