

Rittal – The System.

Faster – better – everywhere.



SK 3312.820

Zračni kanal

State: 11.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3312.820 - Zračni kanal za stensko hladilno enoto Blue e+ IT

Za dovod hladnega zraka pred 482,6 mm (19") etažo v kombinaciji s stensko hladilno enoto Blue e+ IT.



Features

Št. Modela	SK 3312.820
Prednosti	En zračni kanal za različne globine ohišja
Material	Jeklena pločevina, lakirano
Barva	RAL 9005
Obseg dobave	Sestavni deli
Možnosti namestitve	Montaža v spodnje 3 U enote 482,6 mm (19") nivoja
Mere	Širina: 482,6 mm Višina: 3 U
Primerno za	Globina: = 800 mm = 1.000 mm = 1.200 mm
Paketi	1 pc(s).
Neto teža	16,15 kg
Bruto teža	17 kg
Carinska tarifna številka	39269097
ETIM 9	EC011444
ETIM 8	EC011444

Features

ECLASS 8.0

22410601

Opis izdelka

SK IT air duct for Blue e+ wall cooling unit 3312.810, For usage in combination with Blue e+ wall cooling unit 3312.810, Installation in 19" frame