

# Rittal – The System.

Faster – better – everywhere.



## SK 3313.614 Connection hose

State: 5.4.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3313.614 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

## Features

Model No.	SK 3313.614
Design	Rack cooling CW
Product description	The LCU cooling water connection is easily connected to the on-site pipework with the water connection kit. The hoses have a 90° bend on one side and a clamping tray on the other, to allow shortening of the hoses. Allows shortening of the hoses.
Material	NBR (internal) with steel spiral and fabric inlay
Length	2,5 m
Water connections	G ¾" internal thread
Operating temperature range	-30 °C...70 °C
Permissible operating pressure (p. max.)	10 bar
Packs of	2 pc(s).
Net weight	5,08 kg
Gross weight	5,485 kg
Customs tariff number	39173200
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK Connection hose, for LCU CW 3313.610, length 2500 mm