

Rittal – The System.

Faster – better – everywhere.



SK 3352.230

Vario rack-mounted fans for 482.6 mm (19")

State: 2.4.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3352.230 - Vario rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m³/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. Guide frame ensures easy maintenance of the fan.

Features

Model No.	SK 3352.230
Product description	Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.
Benefits	Guide frame ensures easy maintenance and replacement of the fans
Colour	RAL 7035
Supply includes	Fully wired unit ready for connection Terminal strip and assembly parts
Air throughput (unimpeded air flow)	480 m ³ /h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 0.36 A At 60 Hz: 0.33 A
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Dimensions	Width: 482.6 mm Height: 44 mm Depth: 200 mm
Distance between axes of fans	105 mm
No. of fans	3
Noise level	At 50 Hz: 51 dB(A)
Operating temperature range	-10 °C...55 °C
Packs of	1 pc(s).

Features

Net weight	2,5 kg
Gross weight	2,729 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK rack-mounted fan, for 482.6 mm (19"), 480 m ³ /h, 230 V, 1~, 50/60 Hz, WHD: 482.6 x 44 x 200 mm

Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity
