

Rittal – The System.

Faster – better – everywhere.



SK 3378.200 Liquid Cooling Package

State: 31.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3378.200 - Liquid Cooling Package Industrijski LCP Rack

Air/water heat exchanger in TS 8 baying system, useful cooling output 10 kW.

Features

Št. Modela	SK 3378.200
Zasnova	Deli za prenos vode, baker/medenina (Cu/CuZn)
Barva	RAL 7035
Obseg dobave	Ožičenje na priključni letvi Sprednja vrata
Skupna hladilna moč	L 35 W 10 pri 2000 l/h: 9,5 kW
Nazivna delovna napetost	230 V, 1~, 50 Hz/60 Hz
Poraba energije Pel	Pri 50 Hz: 350 W Pri 60 Hz: 350 W
Maks. nazivni tok	Pri 50 Hz: 2,65 A Pri 60 Hz: 2,62 A
Dovoljen delovni tlak (p maks.)	1: 6 bar
Vrsta električne povezave	Connection clamp
Delovni cikel	100 %
Hladilni medij	Water (see Internet for specifications)
Temperatura dovodne vode	7 °C...30 °C
Priključki za vodo	G ¾" internal thread
Delovno temperaturno območje	5 °C...70 °C
Opomba	Pritrditev z vijaki ob straneh
Mere	Širina: 300 mm Višina: 2.000 mm Globina: 600 mm
Stopnja hrupa	60 dB(A)

Features

Predvarovalka	Miniaturni odklopnik/varovalka: 4 A
Nastavitveno območje	20 °C...55 °C
Razred zaščite po IEC 60 529	IP 55
Paketi	1 pc(s).
Neto teža	118 kg
Bruto teža	128 kg
Carinska tarifna številka	84186900
ECLASS 8.0	27180712
Opis izdelka	SK Liquid Cooling Package, Air/water heat exchanger in TS 8 baying system, 9.5 kW, 230 V, 1~, 50/60 Hz, Water-carrying parts: copper/brass , WHD: 300 x 2000 x 600 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity