

Rittal – The System.

Faster – better – everywhere.



SK 3396.554

Aksialni ventilator

State: 25.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3396.554 - Aksialni ventilator

Features

Št. Modela	SK 3396.554
Premer	200 mm
Nazivna delovna napetost	230 V, 1~, 50 Hz/60 Hz
Paketi	1 pc(s).
Neto teža	2,447 kg
Bruto teža	2,847 kg
Carinska tarifna številka	84145925
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704