

# Rittal – The System.

Faster – better – everywhere.



## SV 3431.030

## NH ločilniki, velikost 000

State: 13.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3431.030 - NH ločilniki, velikost 000



## Features

Št. Modela	SV 3431.030
Zasnova	For 60 mm busbar systems
Material	Poliamid, ojačan s steklenimi vlakni Protipožarna zaščita v skladu z UL 94 Kontaki: trd baker s srebrno prevleko
Barva	Ogrodje: RAL 7035 Pokrov: RAL 7001
Za sisteme palic z razmakom med središči	60 mm
Kabelska vtičnica	Bottom
Vrsta električne povezave	Box terminal
Nazivni obratovalni tok maks.	100 A
Nazivna delovna napetost	690 V, 3~
Za velikost NH	000
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 53 mm Višina: 213 mm
Priklop okroglih vodnikov	2,5 - 50 mm <sup>2</sup>

# Features

Za namestitev zbiralnih sponk	Višina: 5, 10 mm
Število polov	3-pole
Round conductor cross-section	2,5 - 50 mm <sup>2</sup>
Paketi	1 pc(s).
Neto teža	0,599 kg
Bruto teža	0,62 kg
Teža bakra (kg na kos)	0,15
Carinska tarifna številka	85369095
ETIM 9	EC000249
ETIM 8	EC001040
ECLASS 8.0	27371401
Opis izdelka	SV NH fuse-switch disconnecter, size 000, 100 A, 690 V, 3-pole, box terminal, cable outlet bottom

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK