

Rittal – The System.

Faster – better – everywhere.



SV 3588.005

Zbiralne sponke E-Cu

State: 2.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3588.005 - Zbiralne sponke E-Cu

Dolžina: 2400 mm/vodnik.



Features

Št. Modela	SV 3588.005
Material	E-Cu F30
Opomba	Lahko se individualno odreže na zahtevano dolžino
Standardi	DIN EN 13 601
Prečni prerez	50 mm x 10 mm
Mere	Dolžina: 2.400 mm
Paketi	2 pc(s).
Neto teža	21 kg
Bruto teža	21,7 kg
Teža bakra (kg na kos)	10,75
Carinska tarifna številka	74071000
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

Features

Opis izdelka

SV Busbar E-Cu, WH: 50x10 mm, L: 2400 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK