

Rittal – The System.

Faster – better – everywhere.



IT 3659.191 Server telescopic slides

State: 27.7.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 3659.191 - Server telescopic slides for IT rack systems and IT racks

Ensure optimum access to the servers, even when built-in. For servers with a maximum width of 430 mm.



Features

| | |
|-------------------------------|--|
| Model No. | IT 3659.191 |
| Design | For 573.65 - 701.65 mm distance between levels |
| Product description | Ensure optimum access to the servers, even when built-in. For servers with a maximum width of 430 mm. |
| Material | Sheet steel |
| Load capacity | 30 kg |
| Note | Only in conjunction with L-shaped mounting angles |
| To fit | Enclosure type: TS TS IT VX VX IT Depth: = 800 mm |
| Packs of | 2 pc(s). |
| Net weight | 2.82 |
| Gross weight | 3.08 |
| PCF per pack (cradle-to-gate) | 6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 73269098 |
| EAN | 4028177964938 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |