## Rittal – The System.

Faster – better – everywhere.





# HD 4000.685 Large enclosure

State: 4.11.2025 (Source: rittal.com/si-sl)



## HD 4000.685 - Large enclosure HD

The HD large enclosure is the bayable enclosure solution for hygienically sensitive areas that are subject to regular cleaning.



#### **Features**

Model No.	HD 4000.685
Material	Enclosure and door: Stainless steel 1.4301 (AISI 304)
	Lock insert HD: Stainless steel 1.4404 (AISI 316L)
	Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
	Mounting plate: Sheet steel
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height
	< 0.8 μm
	Mounting plate: Zinc-plated
	Seal: Blue, dyed (RAL 5010)
Supply includes	Enclosure frame with welded rear panel gland plate
	Door with inserted seal
	R/h door hinge with single-door enclosures, may be swapped to
	opposite side
	Mounting plate
Options	HD supporting structure with levelling
Dimensions	Width: 600 mm
	Height: 1,800 mm
	Depth: 500 mm
Dimensions mounting plate (W x	499 mm x 1,696 mm
H)	
Door opening angle	125°

© Rittal 2025

#### **Features**

Basic material	Stainless steel 1.4301 (AISI 304)
IP protection category to IEC 60	IP 66
529	IP X9
Protection category NEMA	NEMA 4X
Type rating to UL 50E	Type 1
	Type 3R
	Type 4X
	Type 12
Packs of	1 pc(s).
Net weight	74
Gross weight	76.75
Customs tariff number	94032080
EAN	4028177693586
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

## Approvals

	Approvals	UL + C-UL (listed)
--	-----------	--------------------