

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.732 Končni tulci za žice

State: 11.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.732 - Končni tulci za žice ohlapno

S plastično objemko.

## Features

Št. Modela	AS 4050.732
Opis izdelka	S plastičnimi tulci.
Tehnični podatki	Toplotno odporno do 105 °C
Material	E-Cu, galvanizirano Plastični obroč: polipropilen
Barva	Rdeča
Dolžina	8 mm
AWG	18
Notranji premer	3 mm
Za prečni prerez	1 mm <sup>2</sup>
DIN barvna koda	Yes
Opomba	UL certificirano v povezavi z ustreznim orodjem, kot so stroji za stiskanje. Za individualno svetovanje se obrnite na svojega prodajnega svetovalca pri podjetju Rittal.
Standardi	AEH DIN 46228
Za model št.	4051.205 4051.210 4050.452
Obrazec za dostavo	Loose
Paketi	500 pc(s).
Neto teža	0,5 kg
Bruto teža	0,5 kg
Carinska tarifna številka	85369010

# Features

---

ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Opis izdelka	Wire end ferrules for wire processing, 1 mm <sup>2</sup> , red, loose, 8 mm

# Approvals

---

Approvals	UL + C-UL (listed) UR
-----------	--------------------------