

Rittal – The System.

Faster – better – everywhere.



AS 4050.738 Končni tulci za žice

State: 26.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.738 - Končni tulci za žice ohlapno

S plastično objemko.

Features

| | |
|---------------------------|---|
| Št. Modela | AS 4050.738 |
| Opis izdelka | S plastičnimi tulci. |
| Tehnični podatki | Toplotno odporno do 105 °C |
| Material | E-Cu, galvanizirano Plastični obroč: polipropilen |
| Barva | Siva |
| Dolžina | 12 mm |
| AWG | 18 |
| Notranji premer | 2,8 mm |
| Za prečni prerez | 0,75 mm ² |
| DIN barvna koda | Yes |
| Opomba | UL certificirano v povezavi z ustreznim orodjem, kot so stroji za stiskanje. Za individualno svetovanje se obrnite na svojega prodajnega svetovalca pri podjetju Rittal. |
| Standardi | AEH DIN 46228 |
| Za model št. | 4051.205 4051.210 |
| Obrazec za dostavo | Loose (10 packs of 100) |
| Paketi | 1.000 pc(s). |
| Neto teža | 1 kg |
| Bruto teža | 1 kg |
| Carinska tarifna številka | 85369010 |
| ETIM 9 | EC000005 |

Features

| | |
|--------------|--|
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |
| Opis izdelka | Wire end ferrules for wire processing, 0.75 mm ² , grey, loose, 12 mm, 10x100 |

Approvals

| | |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed) UR |
|-----------|--------------------------|