

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.744 Končni tulci za žice

State: 10.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.744 - Končni tulci za žice ohlapno

S plastično objemko.



## Features

Št. Modela	AS 4050.744
Opis izdelka	S plastičnimi tulci.
Tehnični podatki	Toplotno odporno do 105 °C
Material	E-Cu, galvanizirano Plastični obroč: polipropilen
Barva	Rdeča
Dolžina	8 mm
AWG	18
Notranji premer	3,5 mm
Za prečni prerez	1 mm <sup>2</sup>
DIN barvna koda	Yes
Multinorm	Yes
Opomba	UL certificirano v povezavi z ustreznim orodjem, kot so stroji za stiskanje. Za individualno svetovanje se obrnite na svojega prodajnega svetovalca pri podjetju Rittal.
Obrazec za dostavo	Loose
Paketi	500 pc(s).
Neto teža	0,5 kg

# Features

---

Bruto teža	0,5 kg
Carinska tarifna številka	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Opis izdelka	Wire end ferrules for wire processing, 1.0 mm <sup>2</sup> , AWG 18, red, loose, 8 mm (broad shaft)

# Approvals

---

Approvals	UL + C-UL (listed) UR
-----------	--------------------------