

Rittal – The System.

Faster – better – everywhere.



AS 4051.105 LED work light

State: 13.2.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.105 - LED work light for WS 540

For attaching to the table top, with clamping device.



Features

| | |
|----------------------------|---|
| Model No. | AS 4051.105 |
| Product description | For attaching to the table top, with clamping device. |
| Benefits | <p>Bright, glare- and flicker-free lighting, homogeneous and shadow-free</p> <p>Selectable colour temperature between warm white, neutral white and daylight white promotes concentration and reduces symptoms of fatigue</p> <p>Excellent colour fidelity and high contrast</p> <p>Aluminium spring arm with 3D head joint, swivelling and lockable for free positioning of the light source</p> |
| Technical specifications | <p>Spring arm: Length 970 mm</p> <p>Colour reproduction: 94 – 98 Ra</p> <p>Transmission angle: 100°</p> |
| Material | <p>Light housing: Aluminium</p> <p>Glare control: Macrolon</p> |
| Supply includes | <p>LED work light</p> <p>Assembly parts</p> |
| Power consumption | 26 W |
| Length of connection cable | 3 m |
| Connection options | Plug-in power supply (CEE 7/16) with AC adaptor |
| Light | 84 SMD LEDs |

Features

| | |
|-----------------------------|--|
| Protection class | III (SELV) |
| Luminous flux | 2.930 lm |
| To fit Model No. | 4051.100 |
| Operating temperature range | -10 °C...40 °C |
| Rated operating voltage | 110 V - 240 V, 1~, 50 Hz/60 Hz |
| Dimensions | Width: 545 mm Height: 90 mm Depth: 35 mm |
| Packs of | 1 pc(s). |
| Net weight | 2.5 |
| Gross weight | 4.2 |
| Customs tariff number | 94054990 |
| EAN | 4028177957466 |
| ETIM 9 | EC002778 |
| ETIM 8 | EC002778 |
| ECLASS 8.0 | 36629090 |