

Rittal – The System.

Faster – better – everywhere.



AS 4051.537 Konční tulci za žice

State: 11.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.537 - Končni tulci za žice na kolutu

S plastično objemko.

Features

Št. Modela	AS 4051.537
Opis izdelka	S plastičnim tulcem.
Tehnični podatki	Toplotno odporno do 105 °C
Material	E-Cu, galvanizirano Plastični obroč: polipropilen
Barva	Bela
Dolžina	10 mm
AWG	18
Notranji premer	3,4 mm
Rittal barvna koda	Yes
Za prečni prerez	0,75 mm ²
Multinorm	Yes
Opomba	UL certificirano v povezavi z ustreznim orodjem, kot so stroji za stiskanje.
Obrazec za dostavo	Taped
Paketi	4.000 pc(s).
Neto teža	4 kg
Bruto teža	0,584 kg
Carinska tarifna številka	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Opis izdelka

Wire end ferrules 0.75 mm² x 10 mm AWG 18 multinorm, packs of 4,000 pc(s)., colour: white, delivery form: on belt (in accordance with the Rittal colour code), 0.75 mm²

Approvals

Approvals

UL + C-UL (listed)