

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.544 Konční tulci za žice

State: 22.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.544 - Končni tulci za žice na kolotu

S plastično objemko.

## Features

Št. Modela	AS 4051.544
Opis izdelka	S plastičnim tulcem.
Tehnični podatki	Toplotno odporno do 105 °C
Material	E-Cu, galvanizirano Plastični obroč: polipropilen
Barva	Bela
Dolžina	10 mm
AWG	20
Notranji premer	2,9 mm
Za prečni prerez	0,5 mm <sup>2</sup>
DIN barvna koda	Yes
Multinorm	Yes
Opomba	UL certificirano v povezavi z ustreznim orodjem, kot so stroji za stiskanje.
Obrazec za dostavo	Taped
Paketi	4.000 pc(s).
Neto teža	4 kg
Carinska tarifna številka	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Opis izdelka	Wire end ferrules 0.5 mm <sup>2</sup> x 10 mm AWG 20 multinorm, packs of 4,000 pc(s)., colour: white, delivery form: on belt (in accordance with the DIN colour code), 0.5 mm <sup>2</sup>

# Approvals

---

Approvals

UL + C-UL (listed)