

Rittal – The System.

Faster – better – everywhere.



AS 4051.597 Končni tulci za žice

State: 23.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.597 - Končni tulci za žice na kolutu

S plastično objemko.

Features

Št. Modela	AS 4051.597
Opis izdelka	S plastičnim tulcem.
Tehnični podatki	Toplotno odporno do 105 °C
Material	E-Cu, galvanizirano Plastični obroč: polipropilen
Barva	Oranžna
Dolžina	8 mm
AWG	20
Notranji premer	2,6 mm
Rittal barvna koda	Yes
Za prečni prerez	0,5 mm ²
Opomba	UL certificirano v povezavi z ustreznim orodjem, kot so stroji za stiskanje.
Standardi	AEH DIN 46228
Obrazec za dostavo	Taped
Paketi	5.000 pc(s).
Neto teža	5 kg
Bruto teža	0,536 kg
Carinska tarifna številka	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Opis izdelka

Wire end ferrules for crimping machines, 0.5 mm², AWG 20, 8 mm, orange, on belt, 5000 pc(s).

Approvals

Approvals

UL + C-UL (listed)
UR