

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.638 Konční tulci za žice

State: 28.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.638 - Končni tulci za žice ohlapno

S plastično objemko.

## Features

Št. Modela	AS 4051.638
Opis izdelka	S plastičnimi tulci.
Tehnični podatki	Toplotno odporno do 105 °C
Material	E-Cu, galvanizirano Plastični obroč: polipropilen
Barva	Bela
Dolžina	10 mm
AWG	20
Notranji premer	2,6 mm
Za prečni prerez	0,5 mm <sup>2</sup>
DIN barvna koda	Yes
Opomba	UL certificirano v povezavi z ustreznim orodjem, kot so stroji za stiskanje. Za individualno svetovanje se obrnite na svojega prodajnega svetovalca pri podjetju Rittal.
Standardi	AEH DIN 46228
Za model št.	4051.205 4051.210
Obrazec za dostavo	Loose (10 packs of 100)
Paketi	1.000 pc(s).
Neto teža	1 kg
Bruto teža	0,094 kg
Carinska tarifna številka	85369010
ETIM 9	EC000005

# Features

---

ETIM 8	EC000005
ECLASS 8.0	36659290
Opis izdelka	Wire end ferrules for wire processing, 0.5 mm <sup>2</sup> , AWG 20, white, 10 mm, loose (10 packs of 100), 1000 pcs.

# Approvals

---

Approvals	UL + C-UL (listed) UR
-----------	--------------------------