

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.000 Crimping pliers

State: 23.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.000 - Crimping pliers for wire end ferrules

For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.



## Features

Model No.	AS 4054.000
Design	Angled
Product description	For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.
Benefits	Minimal effort required with large wire cross-sections Uniformly high quality compression Marked die stations for precise machining of the relevant cross-sections Releasable ratchet
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Trapezoid crimp
Direction of cable entry	Side
Dimensions	Height: 59 mm Length: 198 mm
AWG	24 - 10
For cross-section	0.25 - 6 mm <sup>2</sup>

# Features

Packs of	1 pc(s).
Net weight	0.439
Gross weight	0.449
Customs tariff number	82032000
EAN	4028177807587
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811