

Rittal – The System.

Faster – better – everywhere.



AS 4054.080 Crimping pliers

State: 6.6.2025 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.080 - Crimping pliers for crimp tab terminals

For use with non-insulated crimp tab terminals



Features

Model No.	AS 4054.080
Design	Angled
Product description	For use with non-insulated crimp tab terminals.
Benefits	Releasable ratchet Marked die stations for precise machining of the relevant cross-sections
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	B-crimp
Dimensions	Width: 18 mm Height: 59 mm Length: 198 mm
AWG	26 - 16
For cross-section	0.1 - 1.5 mm ²
Packs of	1 pc(s).
Net weight	0.433
Gross weight	0.443
Customs tariff number	82032000

Features

EAN	4028177807662
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811