

Rittal – The System.

Faster – better – everywhere.



AS 4054.600 Stranski rezalnik

State: 23.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.600 - Stranski rezalnik

Za bakrene in aluminijaste vodnike.

Features

Št. Modela	AS 4054.600
Zasnova	Ravno
Opis izdelka	Za bakrene in aluminijaste vodnike.
Prednosti	Zagotavlja dolgoročno stabilno rezalno zmogljivost in čist rez Ergonomsko oblikovani ročaji za delo brez utrujenosti in neдрseče površine
Material	Visokokakovostno specialno orodno jeklo
Površinska obdelava	Mat, kromirano
Barva	Ročaj: antracit in Rittal Power Pink
Standardi	Izolacijska zaščita 1000 V VDE
Mere	Dolžina: 160 mm
Za kable s premerom	0,2 - 11 mm
Paketi	1 pc(s).
Neto teža	0,243 kg
Bruto teža	0,253 kg
Carinska tarifna številka	82032000
ETIM 9	EC000165
ETIM 8	EC000165
ECLASS 8.0	21043711
Opis izdelka	Diagonal cutter 0.2-11mm

Approvals

Approvals

VDE