

Rittal – The System.

Faster – better – everywhere.



AS 4054.750

Elektronski stranski rezalnik

State: 30.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.750 - Elektronski stranski rezalnik

S koničasto glavo, rezili pod kotom 21° in majhnim poševnim robom.

Features

Št. Modela	AS 4054.750
Opis izdelka	S koničasto glavo, rezalnimi robovi pod kotom 21° in majhnim poševnim robom.
Prednosti	Enakomerno, gladko odpiranje z odpiralno vzmetjo Ergonomsko oblikovani ročaji Škatlasti spoj za trajno stabilnost in optimalno porazdelitev sile
Material	Visokokakovostno specialno orodno jeklo
Površinska obdelava	Polirano, oljeno
Barva	Ročaj: antracit in Rittal Power Pink
Mere	Dolžina: 115 mm
Paketi	1 pc(s).
Neto teža	0,08 kg
Bruto teža	0,088 kg
Carinska tarifna številka	82032000
ETIM 9	EC000165
ETIM 8	EC000165
ECLASS 8.0	21043711
Opis izdelka	Electronic side cutter