


Rittal – The System.

Faster – better – everywhere.



AS 4055.180

**Komplet luknjačev z razdelilnikom,
metrični**

State: 14.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.180 - Komplet luknjačev z razdelilnikom, metrični za nerjavno jeklo, tridelno, okroglo

Za izrezovanje okroglih izrezov.

Features

Št. Modela	AS 4055.180
Zasnova	Tridelni
Opis izdelka	Za izsekavanje okroglih izrezov. Prebijalo za pločevino se uporablja s ključem ali hidravličnim prebijalom.
Obseg dobave	5 ženskih matric 5 moških matric Plastični kovček
Obdelovalni material	Stainless steel
Za navoje	M16 M20 M25 M32 M40
Opomba	Pri delu s ključi je treba uporabiti napenjalne vijake s krogličnimi ležaji
Max. machinable material thickness, stainless steel / diameter of hole punch / to fit hydraulic screw Model No. / to fit tension screw Model No.	2 mm / 16,2 mm / 4.055.665 / 4.055,632 2 mm / 20,4 mm / 4.055.665 / 4.055,632 2 mm / 25,4 mm / 4.055.665 / 4.055,632 2,5 mm / 32,5 mm / 4.055.663 / 4.055,633 2,5 mm / 40,5 mm / 4.055.663 / 4.055,634
Paketi	1 pc(s).
Neto teža	0,849 kg
Bruto teža	1,098 kg
Carinska tarifna številka	82073010
ETIM 9	EC002121

Features

ETIM 8	EC002121
ECLASS 8.0	21049047
Opis izdelka	Splitter hole punch set, metric for stainless steel, round, with triple splitting
