


**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.532**

**Luknjač z razdelilnikom, okrogel**

State: 28.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.532 - Luknjač z razdelilnikom, okrogel za jekleno pločevino, tridelno

Za izrezovanje okroglih izrezov.

## Features

Št. Modela	AS 4055.532
Zasnova	Tridelni
Obseg dobave	Ženske matrice Moške matrice
Obdelovalni material	Sheet steel
Največja debelina obdelovalnega materiala, jeklena pločevina	3 mm
Ø prebijača	32,5 mm
Za navoje	M32
Opomba	Pri delu s ključi je treba uporabiti napenjalne vijake s krogličnimi ležaji Za nadaljnje mere glejte luknjač za pločevino, okrogel, nerjavno jeklo
Suitable for hydraulic bolt order number	4055.663
Napenjalni vijak (Ø x D)	19 x 55 mm
Ø hidravličnega napenjalnega vijaka	19 mm
Paketi	1 pc(s).
Neto teža	0,2 kg
Bruto teža	0,22 kg
Carinska tarifna številka	82073010
ETIM 9	EC000156
ETIM 8	EC000156

# Features

---

ECLASS 8.0

21049047

---

Opis izdelka

Splitter hole punch, round for sheet steel, with triple splitting