

Rittal – The System.

Faster – better – everywhere.



AS 4055.720

Elektrohidravlična črpalka

State: 30.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.720 - Elektrohidravlična črpalka

Elektrohidravlična črpalka se uporablja za pogon izdelkov serije CW 120-S.



Features

Št. Modela	AS 4055.720
Opis izdelka	Elektrohidravlična črpalka se uporablja za pogon izdelkov serije CW 120-S.
Poraba energije	1,3 kW
Filling volume	3,2 l
Working volume	2,2 l
Flow rate (max.)	1,1 l/min
Oil (type)	HLP 46
Nazivna delovna napetost	230 V, 50 Hz
Nazivni tok	5,65 A
Mere stroja	Širina: 400 mm Višina: 325 mm Globina: 335 mm
Območje podpore	Širina: 402 mm Višina: 342 mm Globina: 397 mm
Dovoljen delovni tlak (p maks.)	700 bar
Paketi	1 pc(s).
Neto teža	32 kg
Bruto teža	34,5 kg

Features

Carinska tarifna številka	84138100
ETIM 9	EC011047
ETIM 8	EC011047
ECLASS 8.0	27301290
Opis izdelka	Electro-hydraulic pump suitable for CW 120 – S and hydraulic cylinders

Approvals

Explanations	Declaration of conformity
--------------	---------------------------