

Rittal – The System.

Faster – better – everywhere.



AS 4055.730 Electro-hydraulic pump

State: 5.4.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.730 - Electro-hydraulic pump

The electro-hydraulic pump is used to drive products in the CW 120-S series.

Features

Model No.	AS 4055.730
Product description	The electro-hydraulic pump is used to drive products in the CW 120-S product series.
Power consumption	1,1 kW
Filling volume	3,5 l
Working volume	2,2 l
Flow rate (max.)	1,1 l/min
Oil (type)	HLP 46
Rated operating voltage	230 V, 50 Hz
Rated current	6,5 A
Machine dimensions	Width: 405 mm Height: 405 mm Depth: 310 mm
Support area	Width: 505 mm Height: 505 mm Depth: 497 mm
Permissible operating pressure (p. max.)	630 bar
Packs of	1 pc(s).
Net weight	32 kg
Gross weight	34,5 kg
Customs tariff number	84135061
ECLASS 8.0	27301290

Approvals

Explanations

Declaration of conformity