

# Rittal – The System.

Faster – better – everywhere.



## SZ 4127.010 Stikalo za vrata

State: 25.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4127.010 - Stikalo za vrata

z montažno opremo, z ali brez priključnega kabla.

## Features

Št. Modela	SZ 4127.010
Zasnova	Brez priključnega kabla
Opomba	Za vgradnjo v VX IT samo skupaj z montažnim nosilcem VX za stikalo na vratih
Nazivna impulzna vzdržna napetost, med fazami	6000 V AC
Nazivna izolacijska napetost	400 V AC
Možnosti namestitve	za LED sistemsko luč za standardno in stropno luč brez integriranega stikala za vrata za hladilne enote in toplotne izmenjevalnike zrak-voda
Električna povezava	240 V AC/6 A 125 V AC/8 A 24 V AC/6 A 24 V DC/6 A
Nazivna delovna napetost	400 V
IP razred zaščite po IEC 60 529	IP 40
Paketi	1 pc(s).
Neto teža	0,068 kg
Bruto teža	0,076 kg
Carinska tarifna številka	85365019
ETIM 9	EC002626
ETIM 8	EC002626
ECLASS 8.0	27189266
Opis izdelka	SZ Door-operated switch, with accessory for interior installation, without connection cable

# Approvals

---

Approvals

CQC  
CQC-CCC  
CSA  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
Declaration of conformity UK