

Rittal – The System.

Faster – better – everywhere.



SZ 4138.180 Standardna luč

State: 27.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4138.180 - Standardna luč

Supply voltage: 120 V AC 60 Hz, 230 V AC 50 Hz

Features

Št. Modela	SZ 4138.180
Zasnova	brez stikala za vrata
Obseg dobave	Standardna luč Luči Sestavni deli
Poraba energije	18 W
Ballast	Magnetic ballast
Možnosti priklopa	Door-operated switch Power supply via connectors Through-wiring (creating rows of lights)
Luči	Fluorescent lamp, base G13
Razred zaščite	I (PE conductor)
Stikalo (tip)	Integral on/off/door-operated switch
Luči – vrsta namestitve	Screw-fastening
Rated impulse withstand voltage, phase to earth	1500 V AC
Nazivna impulzna vzdržna napetost, med fazami	500 V AC
Nazivna izolacijska napetost	500 V DC/1s
Možnosti namestitve	TS vodoravni profil strešnega okvirja: neposreden Navpični profil TS, SE: z adapterskim nosilcem TS SE profili na sprednjem in zadnjem delu strešnega okvirja: z adapterskim nosilcem TS SE profili na strani strešnega okvirja: neposredni AE, CM, TP: z univerzalnim nosilcem AE: s tirnico za notranjo montažo

Features

Mere	Širina: 682 mm Višina: 117 mm Globina: 50 mm
Delovno temperaturno območje	-15 °C...45 °C
Vtičnice	D, earthing-pin (type F, CEE 7/4)
Temperaturno območje shranjevanja	-20 °C...70 °C
Nazivna delovna napetost	230 V, 1~, 50 Hz
Različica vtičnice	D, earthing-pin (type F, CEE 7/4)
Paketi	1 pc(s).
Neto teža	1,74 kg
Bruto teža	1,94 kg
Carinska tarifna številka	94054990
ECLASS 8.0	27189241
Opis izdelka	SZ Standard light, WHD: 682x117x50 mm, 18 W, 230 V, 50 Hz, without door operated switch, with earthing-pin socket

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---